



D-Inside Series Riser Cable

DataTwist 3 UTP, D-Inside Wire and Backbone Indoor Cable, Category 3 Nonbonded-Pair

DataTwist® 3 Cable is a high value UTP cable engineered specifically to perform to Category 3 requirements per ANSI/TIA/EIA—568-C.2. DataTwist 3, D-Inside Wire, D-Flex Plenum and the ATMM Cable Series are rugged multi-pair

cable series that meet and exceed ANSI/TIA/EIA—568-C.2 and CSA T529-95 specifications for Category 3 transmission characteristics and are perfect for use in networking and communication systems.

Backbone Indoor Cable

Belden Part Number	# Pairs	Color	Length	Packaging
DataTwist 3, Nonbonded-Pair, 24 AWG, CMR, Category 3				
1227A1 008U1000	2	Gray	305 m (1000 ft)	UnReel Box
1227A1 Q5HU1000	2	White	305 m (1000 ft)	UnReel Box
1229A1 008U1000	4	Gray	305 m (1000 ft)	UnReel Box
1232A1 0081000	25	Gray	305 m (1000 ft)	Spool
DataTwist 3, Nonbonded-Pair, 24 AWG, CMP, Category 3				
1243A2 009U1000	2	White	305 m (1000 ft)	UnReel Box
1245A2 009U1000	4	White	305 m (1000 ft)	UnReel Box
D-Inside Wire, Nonbonded-Pair, 24 AWG, CMR, Category 3				
DIW2 732U2500	2	Lt. Olive Gray	762 m (2500 ft)	UnReel Box
DIW3 732U1500	3	Lt. Olive Gray	457 m (1500 ft)	UnReel Box
DIW4 732U1000	4	Lt. Olive Gray	305 m (1000 ft)	UnReel Box
DIW4 732U1500	4	Lt. Olive Gray	457 m (1500 ft)	UnReel Box
DIW6 7321000	6	Lt. Olive Gray	305 m (1000 ft)	Spool
DIW12 7321000	12	Lt. Olive Gray	305 m (1000 ft)	Spool
DIW25 732500	25	Lt. Olive Gray	152 m (500 ft)	Spool
DIW25 7321000	25	Lt. Olive Gray	305 m (1000 ft)	Spool
DIW25 732CUT	25	Lt. Olive Gray	Cut to any Length	Spool
DIW50 7321000	50	Lt. Olive Gray	305 m (1000 ft)	Spool
DIW50 7322500	50	Lt. Olive Gray	762 m (2500 ft)	Spool
DIW50 732CUT	50	Lt. Olive Gray	Cut to any Length	Spool
DIW100 732CUT	100	Lt. Olive Gray	Cut to any Length	Spool
DIW200 732CUT	200	Lt. Olive Gray	Cut to any Length	Spool
DIW300 732CUT	300	Lt. Olive Gray	Cut to any Length	Spool
D-Inside Wire, Nonbonded-Pair, 24 AWG, CMP, Category 3				
DFLEX3 732U1500	3	Lt. Olive Gray	457 m (1500 ft)	UnReel Box
DFLEX4 009U1000	4	White	305 m (1000 ft)	UnReel Box
DFLEX4 732U1000	4	Lt. Olive Gray	305 m (1000 ft)	UnReel Box
DFLEX4 732U1500	4	Lt. Olive Gray	457 m (1500 ft)	UnReel Box
DPLN25 7321000	25	Lt. Olive Gray	305 m (1000 ft)	Spool
DPLN25 732CUT	25	Lt. Olive Gray	Cut to any Length	Spool
DPLN50 732CUT	50	Lt. Olive Gray	Cut to any Length	Spool
DPLN100 732CUT	100	Lt. Olive Gray	Cut to any Length	Spool
DPLN200 732CUT	200	Lt. Olive Gray	Cut to any Length	Spool
DPLN300 732CUT	300	Lt. Olive Gray	Cut to any Length	Spool
ATMM/ARMM, Armored, Nonbonded-Pair, 24 AWG, CMR, Category 3				
ATMM25 008CUT	25	Gray	Cut to any Length	Spool
ATMM50 008CUT	50	Gray	Cut to any Length	Spool
ATMM100 008CUT	100	Gray	Cut to any Length	Spool
ATMM200 008CUT	200	Gray	Cut to any Length	Spool
ATMM300 008CUT	300	Gray	Cut to any Length	Spool
ATMM400 008CUT	400	Gray	Cut to any Length	Spool