

Be certain.



Video Distribution Solutions (HD-SDI)

Miniature Coax Cable

Description	Belden Part Number								
	Cable	4.5 GHz Compression				4.5 GHz Crimp			
		BNC Connectors	BNC Locking	Compression Tool	Strip Tool	BNC 3 Piece	Crimp Tool	Strip Tools	Boots
SubMiniature, 28.5 AWG, Precision Video, Non Plenum	179DT	179DTBHD1	179DTBHDL	CPLCRBC-BR	PS59/6/RGB	179DTBHD3	BB3PHCT	BB3PST	SLS-RGB-*
Miniature 23 AWG Precision Video, Non Plenum and Plenum	1855A	1855ABHD1	1855ABHDL	CPLCRBC-BR	PS59/6/RGB	1855ABHD3	BB3PHCT	BB3PST	SLS-RGB-*
Miniature RG59 Precision Video, Non Plenum and Plenum	1855P	1855ABHD1	1855ABHDL	CPLCRBC-BR	PS59/6/RGB	1855ABHD3	BB3PHCT	BB3PST	SLS-RGB-*
5 Cond Miniature 23 AWG Precision Video, Non Plenum, Banana Peel	1855S5	1855ABHD1	1855ABHDL	CPLCRBC-BR	PS59/6/RGB	1855ABHD3	BB3PHCT	BB3PST	SLS-RGB-*
VideoFlex 5 Pack Snake, Non Plenum (1855A)	7789A	1855ABHD1	1855ABHDL	CPLCRBC-BR	PS59/6/RGB	1855ABHD3	BB3PHCT	BB3PST	SLS-RGB-*

* indicate color when ordering, Yellow, Red, White or Black

RG-59 Coax Cable

Description	Belden Part Number								
	Cable	4.5 GHz Compression				4.5 GHz Crimp			
		BNC Connectors	BNC Locking	Compression Tool	Strip Tool	BNC 3 Piece	Crimp Tool	Strip Tools	Boots
RG59 Precision Video, Non Plenum	1505A	1505ABHD1	1505ABHDL	CPLCRBC-BR	PSA59/6	1505ABHD3	BB3PHCT	BB3PST	SLS-59/6
RG59 Precision Video, Plenum	1506A	1506ABHD1	1506ABHDL	CPLCRBC-BR	PSA59/6	1506ABHD3	BB3PHCT	BB3PST	SLS-59/6
RG59 Precision Video, Flexible	1505F	1505ABHD1	1505ABHDL	CPLCRBC-BR	PSA59/6	1505ABHD3	BB3PHCT	BB3PST	SLS-59/6
5 Cond RG59 Precision Video, Non Plenum, Banana Peel	1505S5	1505ABHD1	1505ABHDL	CPLCRBC-BR	PSA59/6	1505ABHD3	BB3PHCT	BB3PST	SLS-59/6
VideoFlex 5 Pack Snake, Non Plenum (1505A)	7796A	1505ABHD1	1505ABHDL	CPLCRBC-BR	PSA59/6	1505ABHD3	BB3PHCT	BB3PST	SLS-59/6

RG-6 Coax Cable

Description	Belden Part Number								
	Cable	4.5 GHz Compression				4.5 GHz Crimp			
		BNC Connectors	BNC Locking	Compression Tool	Strip Tool	BNC 3 Piece	Crimp Tool	Strip Tools	Boots
RG6 Precision Video, Non Plenum	1694A	1694ABHD1	1694ABHDL	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
RG6 Precision Video, Plenum	1695A	1695ABHD1	1695ABHDL	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
RG6 Precision Video, Flexible	1694F	1694ABHD1	1694ABHDL	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
RG6 Precision Video, Dual Link	1694D	1694ABHD1	1694ABHDL	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
RG6 Precision Video, Indoor/Outdoor Waterblocked	1694WB	1694ABHD1	1694ABHDLW*	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
5 Pack Snake, Non Plenum (1694A), Banana Peel	1694S5	1694ABHD1	1694ABHDL	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
5 Pack Snake, Plenum (1695A), Banana Peel	1695S5	1695ABHD1	1695ABHDL	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
VideoFlex 5 Pack Snake, Non Plenum (1694A)	7712A	1694ABHD1	1694ABHDL	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6

*Connector is also watertight.

RG-7 Coax Cable

Description	Belden Part Number			
	Cable	Connectors 4.5 Gig BNC Compression	Compression Tool	Strip Tool
RG7 Precision Video, Non Plenum	1794A	1794ABHD1	CPLCRBC1794	PS-11

RG-11 Coax Cable

Description	Belden Part Number					
	Cable	Connectors 3.0 Gig BNC Compression	BNC Compression Tool	Connectors 3.0 Gig F Compression	F Compression Tools	Strip Tool
RG11 Precision Video, Non Plenum	7731A	FSNS11QBNC	SNSUNI, CPLCCT-11BNC	716SNS1P11HQ	SNSUNI, L3011B, CPLCCT-SS59/11	PS-11
RG11 Precision Video, Plenum	7732A	FSNS11HBNCPLA	SNSUNI, CPLCCT-11BNC	716SNS1P11HPLA	SNSUNI, L3011B, CPLCCT-SS59/11	PS-11
RG 11 Precision Video, Waterblocked	7731WB	FSNS11QBNC	SNSUNI, CPLCCT-11BNC	716SNS1P11HQ	SNSUNI, L3011B, CPLCCT-SS59/11	PS-11