

Faster.
Easier.
Better.




Grounding and Bonding

Options

Description	Belden Part Number
19" Horizontal Isolated Copper Ground Bar, .25" Thickness x 1" W, Tapped 10-32	9714-0190
Grounding/Bonding Strap Kit (11" strap with hardware)	XBS-11-0001
Grounding/Bonding Strap Kit (18" strap with hardware)	XBS-18-0002
Grounding/Bonding Strap Kits	
Bonding Strap Kit (11" strap with hardware and anti-oxidation compound)	XBS-11-0001
Bonding Strap Kit (18" strap with hardware and anti-oxidation compound)	XBS-18-0001
Grounding Lug Kit (Ground Lug and 1/4-20 Kep Nut)	20128-KIT

Notes:

Bonding strap kit is included with enclosure doors, sides and top panels.
Grounding lug kit is for use with rack and enclosure welded ground studs.



19" mount grounding bar is 0.25" thick x 1.25" wide, with #10-32 tapped holes; isolating mounts with hardware are included.

Mounting Hardware

Application

Included adjoining hardware for ganging of racks and enclosures, plus a variety of bolts, screws and nuts for mounting of active and passive networking devices into enclosures and racks.

Description	Quantity/Package	Belden Part Number
10-32 Hardware		
10-32 Mounting Screws	50	8911-0100
10-32 Cage Nuts (for use with square hole rails)	50	8915-0100
10-32 Cage Nuts (for use with square hole rails)	20	8915-0220
10-32 Clip Nuts	20	8915-0320
12-24 Hardware		
12-24 Mounting Screws	50	8917-0100
12-24 Cage Nuts (for use with square hole rails)	50	8917-0220
12-24 Clip Nuts	20	8917-0320
M6 Hardware		
M6 Cage Nut (for use with square hole rails)	50	8913-0100
M6 Cage Nut (for use with square hole rails)	20	8913-0220
M6 Clip Nut	20	8913-0320
M6 x 16 mm Mounting Screw	50	8914-0100
Cable Ties		
Velcro Cable Ties, 8"L x 0.5"W, 25 per Roll	25	AX100783
Velcro Cable Ties, 12"L x 0.5"W, 25 per Roll	25	AX100784
12" Fiber Optic Cable Manager	1	AX102516
24" Fiber Optic Cable Manager	1	AX102517
Quick Mount Velcro Saddle with Fastener	10	XMFCTM



AX102516 Cable Slack Management Ring - 12" diameter

Adjoining Hardware

Description	Enclosure Series	Belden Part Number
Enclosure Adjoining Kit (4) 5/16-18 Hex Head Bolt; (4) 5/16-18 Hex Nut; (8) 5/16 Flat Washer	XS, XN, XM, XSS, XNX	8910-0100
Enclosure Adjoining Kit for NEMA 12 (4) 5/16-18 Hex Head Bolt; (4) 5/16-18 Hex Nut; (8) 5/16 Flat Washer, includes Gasketing	XNM	XNM-0100
Bolt-Together Kit for XSF Frames (incl. hardware)	XSF	XSF BK01
Adjoining Kit (4) 1/4-20 x 5/8 Carriage Bolt; (4) 5/16 External Tooth Lock Washer; (4) Whizlock Nuts	XMFBK01	XMFBK01
Loaded Rack Application Bolt Kit (4) 12-24 x 1 3/4 Screw; (8) External Tooth Washer; (4) 12-24 Hex Nuts; (4) .5 x .125"W Tubing Nylon	XMFBK02	XMFBK02
Adjoining Kit (4) 1/4-20 x 5/8 Whizlock Bolt; (4) 1/4-20 Whizlock Nut	XME, XMER	XMEBK01
Joining Kit (4) 5/16 x 1 Bolt, (8) 5/16 Washers, (4) 5/16 Nuts	—	XBK01

Note:

Adjoining hardware is included with the enclosures.