



Belden's FiberExpress (FX) Fusion Splice-On connectors combine the benefits of fusion splicing with the simplicity of a field-installable connector to expand your options for field termination and improve installation performance and reliability over mechanical splice connectors. No crimping, polishing or adhesives are required for termination, minimizing installation errors.

FX Fusion Splice-On Connectors



BENEFITS

- Futureproofing to ensure networks with high bandwidth and high-speed transmission
- Reduced hardware costs versus traditional pigtails
- Improved first pass yields
- Robust, reliable installation for indoor and outdoor environments
- Eliminates cable shorts and excess slack



FEATURES

- Fusion technology that delivers better insertion and return loss performance versus mechanical splice connectors
- Internally protected splice eliminates need for splice enclosures and splice trays
- Highly automated splicing tools
- Compatible splicer accessories
- Solutions for OM1, OM3, OM4, OS2 and OS2 APC meet ANSI/TIA-568-D3 standards



FX Fusion Splicer



BENEFITS

- Delivers affordable, high-quality performance
- Provides consistent and reliable terminations
- Eliminates splicer errors due to dust and other contaminants for perfect cladding alignment



FEATURES

- Active cladding alignment
- Single fiber splicing
- Lightweight (only 2.5 lbs)
- Large, user-friendly display
- 200 splice cycles per battery charge
- Supports splice-on connectors and pigtail splicing



*GR rating will be available in Fall 2017

Ordering Information

FX Fusion Multimode Connectors

Description	Belden Part Number		
	Multimode, OM1 - Beige	Multimode, OM3/OM4 - Aqua	Multimode, OM4 - Erika Violet
LC with 900 µm Boot, 1/Pack	FT1LC900FS01	FT3LC900FS01	FT4LC900FS01
SC with 900 µm Boot, 1/Pack	FT1SC900FS01	FT3SC900FS01	FT4SC900FS01

FX Fusion Singlemode Connectors

Description	Belden Part Number	
	Singlemode, OS2 - Blue	Singlemode, OS2/APC - Green
LC with 900 µm Boot, 1/Pack	FTSLC900FS01	FTSLB900FS01
SC with 900 µm Boot, 1/Pack	FTSSC900FS01	FTSSB900FS01

To use the tailored *SmartPart* configuration matrices, make a selection from each category and combine to form a custom part number. See example(s) below.

Tailored FX Fusion Connectors

Part number example from configuration shown below:

FT3LC900FS01

FT	3	LC	900	F	S01
Field Termination	Fiber Type	Connector	Cable Type	Family	Packaging
	1 OM1	LC LC Simplex	900 Tight Buffer	F Splice-On	S01 Single Pack
	3 OM3	LB LC/APC Simplex	2MM Jacketed		
	4 OM4	SC SC Simplex			
	S OS2	SB SC/APC Simplex			

2MM will be available in Fall 2017

FX Fusion Accessories

Description	Belden Part Number
Precision Tool Kit	FXFSTOPTK
Standard Tool Kit	FXFSTOSTK
Precision Cleaver	FXFSTOPCL
Standard Cleaver	FXFSTOSCL
Splice Holder Family 1	FXFSSHFM1*
Splice Holder Family 2	FXFSSHFM2
Slitter for Jacketed Fiber	FXFSTOSLT
Splicer Kit (includes splicer and all of the parts listed to the right)	FXFSTOSPL

*FXFSSHFM1 Holder compatible with Fujikura 60S, Fujikura 70S, Sumitomo Q101, among many others. Visit www.belden.com/splice-on for more details.

FX Fusion Splicer Kit Replacement Parts

Description	Belden Part Number
AC Adapter/Charger	FXFSTOSAC
Shoulder Strap	FXFSTOSSS
Cleaning Brushes	FXFSTOSCB
Fiber Holders/Clamps	FXFSTOSFC
Spare Electrode	FXFSTOSSE
Cooling Tray	FXFSTOSCT
Carrying Case	FXFSTOSCC
User Guide CD	FXFSTOSCD
Keys for Lock	FXFSTOSKY
Screwdriver	FXFSTOSSD
Yellow Tackle Box	FXFSTOSTB

To learn more call us at
1.800.BELDEN.1 or visit
www.belden.com/splice-on

© Copyright 2017, Belden Inc.
FX Fusion Connectors_PB00100_V2_ECOS_BDC_0617_A_AG